DISCRETE SAMPLING KIT (WHABS020D - 25mm)



This component is used when it is necessary to sample through a suspended ceiling. The capillary Tee piece fits onto the pipe run. There followed by a 2 meter 10mm OD nylon tube which links into the discrete head. The discrete cap is supplied with a solid head, which will necessitate a hole being drilled to the required size by the installer. The discrete end cap is held in place by a hole in the ceiling tile.

Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

